



valid until: April 13, 2031

# Fraunhofer

## TESTED<sup>®</sup> DEVICE

DYDEN CORPORATION  
RMCV Ø 6.5mm

**Report No. DY 2603-1735**

DUPLICATE

Statement of  
Qualification

Single product  
Particle Emission  
in Cleanroom  
(atmospheric)

# Statement of Qualification · Single product

**Customer**  
 DYDEN CORPORATION  
 Factory Automation & Robot Cable Division Tomoya Koike  
 2-15-1 Minami, Kurume-shi  
 830-8511 Fukuoka  
 Japan

**Tested product**  
 Category: Energy Supply  
 Subcategory: Cable Systems  
 Product name: RMCV Ø 6.5mm  
 (manufacturing date: 4/2025; color: black; article number: DY202504-01)

## Test result / Classification

The cable RMCV Ø 6.5mm is suitable for use under the specified test parameters (room temperature: 22 °C ± 0.5 °C; relative humidity: 45 % ± 5 %) in cleanrooms of the following Air Cleanliness Classes according to ISO 14644-1:

Test parameter(s)	Air Cleanliness Class
$v_1 = 0.5 \text{ m/s}; a_1 = 1.0 \text{ m/s}^2$	1
$v_2 = 1.0 \text{ m/s}; a_2 = 2.0 \text{ m/s}^2$	1
$v_3 = 2.0 \text{ m/s}; a_3 = 4.0 \text{ m/s}^2$	1
<b>Overall result</b>	<b>1</b>

Please note: Transport damages, incorrect installation, aging behavior, corrosion etc. can influence the test result.

## Random sampling of particle emissions (airborne) at representative sites in cleanroom under atmospheric conditions

Standards/guidelines: ISO 14644-1, -14  
 The norms stated generally refer to the version valid at the time of the tests.

Test equipment: Optical particle counter:  
 LasAir II 110 and LasAir III 110 with measuring ranges  $\geq 0.1 \mu\text{m}$ ,  $\geq 0.2 \mu\text{m}$ ,  $\geq 0.3 \mu\text{m}$ ,  $\geq 0.5 \mu\text{m}$ ,  $\geq 1.0 \mu\text{m}$  and  $\geq 5.0 \mu\text{m}$

Test environment parameters:

- Cleanroom Air Cleanliness Class (according to ISO 14644-1):..... ISO 1
- Airflow velocity:..... 0.45 m/s
- Airflow pattern:..... vertical laminar flow
- Room temperature: ..... 22 °C ± 0.5 °C
- Relative humidity: ..... 45 % ± 5 %

Test procedure parameters:

- Energy chain: ..... E6.29.100.150.0
- Bending radius: ..... r = 150 mm
- Stroke length: ..... s = 820 mm
- Parameter Set 1:.....  $v_1 = 0.5 \text{ m/s}; a_1 = 1.0 \text{ m/s}^2$
- Parameter Set 2:.....  $v_2 = 1.0 \text{ m/s}; a_2 = 2.0 \text{ m/s}^2$
- Parameter Set 3:.....  $v_3 = 2.0 \text{ m/s}; a_3 = 4.0 \text{ m/s}^2$

The measuring devices used for the qualification tests are calibrated at regular intervals; their results can be traced back to national and international standards. In cases where no national standards exist, the test procedure implemented complies with the technical regulations and norms applicable at the time of the test. The relevant documentation can be viewed on request at any time.

DUPLICATE

DUPLICATE